



MODELS C1300 / HC1300C

Hot Water Dispensers

APPLICATION: Designed for large volume usage of steaming hot water. Up to 200°F (average) hot water per hour is provided by the system's 2/3-gallon tank. Saves time, work and water – heat only the water you use.

FEATURES

- Foodservice grade heating element
- Swiveling gooseneck spout travels 90° to provide clearance for large vessels
- Easy-action lever with automatic shut-off for hot
- Dual cold lever (HC model) with optional filtration system
- Durable all brass faucet with polished chrome finish
- 2/3-gallon stainless steel tank construction for longer life
- Easy-to-adjust temperature control on front panel
- Mounts in standard sink opening or 1-3/8" drilled hole
- Tool-free tank connections and dry start protection for easy installation
- 1-year full-service limited warranty on parts and labor




SPECIFICATIONS

Capacity	2/3-gallon tank dispenses up to 200°F (average) hot water
Electrical	115 Volts A.C., 1300 Watts, 11.3 amp heating element with 36" cord and grounded plug
Thermostat	Snap action, adjustable from 160°F to 210°F (factory pre-set at approximately 200°F)
Insulation	Meets U.L. 94HF-1 flammability specification
Valve	Instant, self-closing
Recommended Supply Pressure	25-80 psi
Shipping Weight	Approximately 11.5 lbs.

To ensure optimum performance, maximum distance between tank and base of faucet should be 14-1/2" or less.

DIMENSIONS



Certification Links: www.pld.iapmo.org, www.nsf.org/certified-products-systems

1.800.845.8345
www.insinkerator.com/foodservice

F513-23D-83-10

A complete collection of our product drawings is available for download at the **InSinkErator Revit/CAD Library**, which can be found at www.insinkerator.com/foodservice. Product information is also accessible on **The KCL CADalog**. More information is available from KCL at www.kclcad.com.

