

CONTROL CENTER MODEL MRS

3-BUTTON • MANUAL REVERSE


SPECIFICATIONS

- 3-button switch with FWD/STOP/REV
- Stainless steel construction
- NEMA 4
- · Manual reverse allows increased cutting element life and reduces jams
- · Magnetic starter/provides automatic shut-off in case of power interruption
- · Operates on line voltage

VOLTAGE/PHASE AVAILABILITY

Model	Voltage/Hz	Phase	Disposer Models
MRS-14	120V, 50/60 Hz	1 Ph	SS-100 to SS-200
MRS-15	208-240V, 50/60 Hz	1 Ph	SS-100 to SS-200
MRS-16	208-240V, 50/60 Hz	3 Ph	SS-100 to SS-1000
MRS-17	380-460V, 50/60 Hz	3 Ph	SS-100 to SS-1000

RECOMMENDED INSTALLATION




NOTE: The MRS control center should be mounted 1-1/2" (38.1 mm) back from the front surface of the table.





DIMENSIONS



A complete collection of our product drawings is available for download at the InSinkErator Revit/CAD Library, which can be found at www.insinkerator.com/foodservice. Product information is also accessible on The KCL CADalog. More information is available from KCL at www.kclcad.com.



in sink erator[.]

1250 International Drive Mount Pleasant, WI 53177 TEL: 800-845-8345

www.insinkerator.com/foodservice







InSinkErator ©2023

Printed in USA Form No. F453-23C-83-85