




Dimensions



Job Specifications

ADVANCED SERIES

PRO Cover Control

Submittal Sheet

This model offers the following features and benefits:

- 3/4 HP long-lasting, Dura-Drive[®] induction motor
- Quiet SoundSeal Technology® delivers quiet disposal operation
- Advanced Grind for tough and fibrous food scraps
- 3-Stage MultiGrind® Technology: Finest grind designed to prevent clogs
- EZ Connect Disposal easily connects to a hardwire connection or outlet
- Removable, Diswasher Safe, Antimicrobial Quiet Collar[®] Sink Baffle
- Safe for use with properly maintained septic tanks
- Units Available: PRO Cover Control with EZ Connect Adapter or PRO Cover Control with EZ Connect Cord

Sample Specification

Food Waste Disposer(s) shall be InSinkErator PRO Cover Control, batch feed, with 3/4 HP. motor, stainless steel grinding elements with two stainless steel 360° swivel lugs. Exclusive self-service wrench.

Warranty

10-Year We Come to You[®] Limited In Home Warranty

* The complete InSinkErator warranty is included in the Care & Use Booklet packed with each unit.



1-800-558-5700 www.insinkerator.com

Specifications

Type of Feed	Batch
On/Off Control	T-Handle Stopper Switch
Motor	Single Phase
HP	3/4
Volts	120
HZ	60
RPM	1725
Amp. (Avg. Load)	9.5
Time Rating	Intermittent
Lubrication	Permanently Lubricated Upper & Lower Bearings
Shipping Weight (Approx.)	20.7, 20.9
Overall Height	14.95
Motor Protection	Automatic Reset
Average Water Usage	Approx. 1 Gallon per Person Per Day
Average Electrical Usage	3-4 KWh per Year
Drain Connection	1-1/2" cushioned slip joint
Dishwasher Drain Connection	Yes

