




## **Dimensions**



Sink Hole	Standard
Diameter	Sink Hole
Required	25-125 psi
supply	(172-862 kPA
pressure	or 1.7-8.6 bar)
Backsplash Clearance	Minimum 2" required from sink hole center to backsplash
Counter	Maximum
Thickness	of 3"

Compression

1-1/4" - 1-1/2"

Supply Connection

Required

# Melea™

# Cool Filtered Water Dispenser Faucet

F-C1400

### **Features**

- · Dispenses cool, filtered water
- · Single hole installation
- Spout swivels 360-degrees for convenience
- · Flexible connectors for easy installation
- Constructed of high quality, low lead brass
- 40° turn ceramic disc valve
- 0.75 gallons per minute maximum flow rate at 60 psi
- For use with InSinkErator® filtration system (sold separately)
- · Unit not for commercial/industrial use

#### Finishes:


Chrome, Satin Nickel, Matte Black, Oil-Rubbed Bronze and Polished Nickel

#### Warranty:

We Come To You® 5-Year In-Home Limited Warranty. Covers parts and labor.

\* The complete InSinkErator warranty is included in the Care & Use booklet with each unit.

## **Job Specifications**



USA 1-800-558-5700 www.insinkerator.com