PRODUCT SPEC SHEET

Showroom Collection: F-GN2215 Tuscan steaming hot water tap



Special edition F-GN2215 Tuscan steaming hot water tap

Classic and nostalgic, the F-GN2215 provides the perfect combination of traditional style and functionality. Pure convenience is guaranteed from the F-GN2215, which dispenses filtered steaming hot water at up to 98°C.

Features

- Dispenses up to 98°C filtered steaming hot water, which is perfect for hot drinks and countless kitchen tasks
- Safe, multi step hot water handle
- Additional to your main tap
- Efficient use of space and time

- Easy to install
- Available in chrome and brushed steel
- 2 year tap and tank guarantee





PRODUCT SPEC SHEET

Showroom
Collection:
F-GN2215 Tuscan
steaming hot
water tap

Specifications

- Required Hole Diameter: 32mm 38mm
- Complete installation kit for solid surface mount
- Capacity: 2.5 litre stainless steel tank
- Required hole diameter: 32-38mm
- 172-862 kPa (1.7-8.6 bar) (25-125 psi)
- Required supply pressure (hot): 50 kPa (0.5 bar) (7 psi)
- Compatible with InSinkErator hot water tank and F-701R water filter

Dimensions (mm)





InSinkErator Suite 10, Building 6 Hatters Lane Crostey Green Business Park Watford, Herts WD18 8YH United Kingdom

Sales tel: (0) 1 923 297 880 Service tel: (0) 800 389 3715 www.insinkerator.co.uk InSinkErator Emerson Electric Co. 4700 21st Street Racine, WI 53406-5093 USA Sales/Service tel: 262-554-5432 www.insinkerator.com/worldmap.html

