

# **CONTROL CENTER MODEL MS**

#### SINGLE DIRECTION

### **SPECIFICATIONS**

- Single direction only
- Push button ON/OFF switch
- High impact polycarbonate construction
- NEMA 4
- Magnetic starter/provides automatic shut-off in case of power interruption
- · Operates on line voltage


#### **VOLTAGE/PHASE AVAILABILITY**

Model	Voltage/Hz	Phase	Disposer Models
MS-7	120V, 50/60 Hz	1 Ph	SS-100 to SS-200
MS-8	208-240V, 50/60 Hz	1 Ph	SS-100 to SS-200
MS-9	208-240V, 50/60 Hz	3 Ph	SS-100 to SS-1000
MS-10	380-460V, 50/60 Hz	3 Ph	SS-100 to SS-1000






#### RECOMMENDED INSTALLATION



## **DIMENSIONS**



NOTE: Use a #8 screw to mount control.

A complete collection of our product drawings is available for download at the **InSinkErator Revit/CAD** Library, which can be found at www.insinkerator.com/foodservice. Product information is also accessible on **The KCL CADalog**. More information is available from KCL at www.kclcad.com.









